

Datasheet 20160302

Sonimix 3057 Self Regenerable Zero Air Generator

Description

The **self regenerable zero** air **generator Sonimix 3057** is the ideal companion of the sonimix machines. It allows to aliment in carrier gas the calibration systems + GPT and gas dividers without the need of expensive and cumbersome zero air pressurized cylinders.

The functions of the **Sonimix 3057** are to filter, dry and clean the ambient air of polluants such as HC, CH4, CO; NO, NO2, O3 and SO2.

The sonimix 3052/57-5Nl/min and 10 Nl/min have an internal compressor included. The sonimix 3052/57-30 Nl/min need an external compressed air source (min 6 bars).



Functioning principle:

The ambient air is pressurised up to 10 bar (140 psi) with an internal compressor or external compressed air sourced. It goes through a dust filter with automatic purge. The drying process is achieved by a self regenerable molecular sieve filter.

Low maintenance



No cylinders

The dry air is processed through different modules: the first scrubber eliminate the NO, the second one is an activated charcoal scrubber to remove the remanent HCnm, SO2, NO2, O3... and the third one is an hot catalysis system which remove the CH4 and the CO. The purified air goes to a pressure regulator and is available at the outlet.

The regeneration process of the scrubbers is reached by using a pair of filters which are regenerated in alternance with reverse gas flow and a pressure swing system.

All the control parameters such as regeneration phases, low input pressure, temperature of the oven are **controlled and monitored by the included microprocessor.**

Applications



The Sonimix 3052/3057 can be used to supply:

- Combustion Air for FID
- Dried Air for ozone generators and NOx analysers
- Zero Air for all gas analysers
- Carrier gas to aliment the sonimix calibrators or gas diluters



Representantes / Distribuidores Exclusivos
Buenos Aires, Argentina

Tel.: (54 - 11) 5352-2500 Email: info@dastecsrl.com.ar Web: www.dastecsrl.com.ar

Specifications

Flow generated (at atmospheric

conditions)

0 to 5 NI/min / 0 to 10 NI/min / 0 to 30 NI/min : Need compressed Air quality ISO8573-1:2010

Class 1.2.1

Outlet pressure:

adjustable between 1 and 3.5 bar

Remaining level of pollutants:

SO2 & O3 < 1 $\mu g/m3$ (0.5 ppb) NO & NO2 < 1 $\mu g/m3$ (0.5 ppb) + Cnm < 0.02mg/m3 (50 ppb)

HCm < 0.02mg/m3 (50 ppb) if catalysis oven installed

BTEX < 1 ppb

CO < 0.06 mg/m3 (50 ppb) if catalysis oven or cold filter installed

CO2 < 10 ppm

Remaining moisture level: H2O < 100 ppm (-40°C DP)

Functionning temperature: 5 to 40 °C

Stabilisation time after the start

of the compressor:

< 10 min (<15 min if catalysis oven installed)

Life time of the scrubbers: for a daily use of 1 hour, an annual preventive maintenance is suggested

Command mode: Electrical consumption : with an ON/OFF switch placed at the back 220 VAC/ 50 W (200 W if catalysis oven installed) with quick connect and double ring system

Dimensions of casing:

Gas connections:

19 inches, 3 U, 50 cm deep or portable casing as potion

Options - Accessories - Spare parts

Models:		Consumables:	
6800 10 000	Sx 3052/3057 5NI/min	6700 13 870.1	Set of the consumables filters for the
6800 10 001	Sx 3052/3057 10NI/min		annual maintenance (5 & 10 NI/min)
6800 10 002	Sx 3052/3057 30NI/min	6700 13 871	Set of the consumables filters for the annual maintenance (30 NI/min)
Options:		6700 13 872	Kit of diaphragm and valves for the
6800 10 005	Internal compressor 5NI/min		compressor
6800 10 006	Internal compressor 10 NI/min	3742 49 001	Filter for automatic purge V5
		6704 06 176	Refill for CO filter
6800 08 017	Catalyser oven for CO & CH4 for		
	5NI/min and 10 NI/min		
6800 08 018	Catalyser oven for CO & CH4 for		
	5NI/min and 10 NI/min		
6800 10 004	Cold Filter for CO		
6800 10 019	Second outflow regulated line		
6800 10 000	Portable casing		
6700 13 867	Voltage 230V / 50/60 Hz		
6700 13 868	Voltage 115V / 60 Hz		
6700 13 869	Voltage 100V / 60 Hz		



Representantes / Distribuidores Exclusivos

Buenos Aires, Argentina Tel.: (54 - 11) 5352-2500 Email: info@dastecsrl.com.ar Web: www.dastecsrl.com.ar

